



TOCHIGIYA CO.,LTD.

Quick Fastening Anywhere

Reusable

RoHS Compliant

NEW

Hook-and-Loop Fastener

Fasten at Any Position

With Square Ring

Soft and Non-Damaging



A reusable fastening band with combined hook-and-loop functionality, fastenable at any position.



Includes a square ring for immediate use.
Available in 40 cm and 20 cm lengths.
Custom size options available




Polyester material with a soft, loop-dominant surface that is gentle on skin and other materials.

Applications


Suitable for bundling cables, devices, and more.

For Cable




Box

For Transport



Dron

For Unit



Laboratory Equipment


TM-375

Hook-and-Loop Fastener



Model No.	A
TM-375-1	400
TM-375-2	200

Product Details



Since the loop side is formed higher than the hooks, press firmly when fastening.
Do not use with hook-and-loop fasteners other than this product.
Use for supporting heavy loads is not recommended.

Adhesive Strength (Engagement Force)

Test Method: JIS L 3416:2000

Tensile Shear Strength (Shear Strength)		Peel Strength (Peeling Force)	
	N/cm^2 (Kgf/cm ²)		N/cm (gf/cm)
	≥ 10.2 (1.03)		≥ 1.01 (102)



※Data based on standard values of Kuraray Fastening Co., Ltd.

Retention Rate of Adhesive Strength (Repeated Peel Durability)

Test Method: JIS L 3416:2000

Number of Peel Cycles	Tensile Shear Strength (Shear Strength)	Retention Ratio(%)	Peel Strength (Peeling Force)	Retention Ratio(%)
2,000 times	≥ 60%		≥ 60%	

※Data based on standard values of Kuraray Fastening Co., Ltd.



Custom lengths and colors are available.
Please feel free to contact us.

TOCHIGIYA TOCHIGIYA CO.,LTD.

<https://tochigiya.jp/shop/>



TOCHIGIYA ONLINESHOP

search

2D/3D CAD data available for download (PC access only)